




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT P/N | WEIGHT |
|-------------|-----------------------------------|
| CFPGFB3** | .32 LB/10 PCS (144.4 g/10 PCS) |

- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY. OF SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 - DASHED LINES INDICATE BREAK OFF LINES.
 - DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD FILENAME/LAYERS

M00130BA_DC_00A.PRT (1)

PANDUIT

CORP. TIMLEY PARK, ILLINOIS

ACKERMAN FLOOR BOX PLATE
(CFPGFB3**) CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.XX) ± .03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

JSP

SCALE

NONE

DATE

3-19-98

DWG NO.

00130-02

DWG

A

ABS

CHECKED BY

JSP

DATE

3-19-98

CUSTOMER

SUP

ECN

CHK

CHK

DESCRIPTION

RELEASED TO PRODUCTION.

BY

JSP

DATE

3-19-98

REV

R