
+

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WE I GHT				
NKBNCM**Y	.36 LB/10 PCS (165 g/10 PCS)				

## NOTES:

- 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
- 4. PART INCLUDES:
  - 1 MODULE BASE
  - 1- BNC COUPLER (ASSEMBLED TO MODULE BASE)



.86 [21.8]	
.64 [16.3]	.79 [20.0] .79 [20.5]

										MODEL FILENAME			_	
									MODEL PILENAME	M00661ZG_BNC_03.PRT		SIZE		
										DRAWING FILENAME	M02479HU_205	5_00A.PRT		
										NE	NETKEY 50ohm BNC COUPLER			
										MODULE CUSTOMER DRAWING				
												I.I. NUMBER	A	
											INLEY PARK, IL 60477	PRODUCT SPEC	A	
											ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:	WORK INSTRUCTION	A	
										THIRD ANGLE PROJECTION	(.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	SCALE NON	ΝE	
										DRAWN BY JSP	MATERIAL:	PART NO. NKBNC	:M**Y	
R	4-24-06	JsP		RELEASED TO PRODUCTION	02479-205					<b>DATE</b> 4 - 24 - 06	ABS	DRAWING NO.		
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP	отн	CHK .D	· <del>-</del>	02479	-205	