



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


.54 REF.
[13.69]



.87 REF.
[21.97]




.67 REF.
[17.03]



PSL-DCPL

3.00 REF.
[76.20]



.75 REF.
[19.05]

KEY

CAD FILENAME/LAYERS I00913AC_C10608_DCPL_CD_02.prt

PANDUIT CORP. TINLEY PARK, ILLINOIS

PSL-DCPL
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .05 (XXX) ± .010
(.XX) ± .02 ANGLES ± 2°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

2	04/01/08	MROB		DRAWING SIZE WAS 'B'	5380	2		
1	03/14/08	MROBMSAD		UPDATED REFERENCE PARTS. REMOVED DCPLR. DRAWING SIZE WAS 'C'	5344	1		
0	08/24/07	MROBMSAD		DRAWING RELEASED	5120	0		

DESCRIPTION

ECN - R

CUST

SUP

DRAWN BY
MROB

DATE
08/24/07

CHK'D
MSAD

MAT'L: LOCK-IN
POLYCARBONATE
KEY
10% GF NYLON

SCALE 1.5:1

DRAWING NO.
C10608

DWG
A
SIZE