


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- △ B 3. TERMINATED WITH (8 POSITION) MODULAR PLUGS AT BOTH ENDS PER T568B.
- 4. CONSTRUCTED WITH 24AWG STRANDED CAT5e UTP LSZH PATCH CABLE
- 5. MATERIALS:
PLUG: POLYCARBONATE
- 6. NOMINAL CABLE DIAMETER IS 0.215 IN (5.46MM).

PLUG POSITION	CABLE WIRE
1	WHITE/GREEN
2	GREEN
3	WHITE/ORANGE
4	BLUE
5	WHITE/BLUE
6	ORANGE
7	WHITE BROWN
8	BROWN

CABLE COLORS **	= COLOR
WHITE	WH
INTERNATIONAL GRAY	IG
BLUE	BU
RED	RD
GREEN	GR
ORANGE	OR

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

DRAWING FILENAME M02479MJ_DC323/00B		SIZE A
TX5e UTP PATCH CORDS (LSZH) CUSTOMER DRAWING		
<p>PANDUIT[®] CORP. TINLEY PARK, IL 60477</p>	I.I. NUMBER	
	PRODUCT SPEC	
<p>THIRD ANGLE PROJECTION</p>	<p>ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.</p> <p>DIMENSIONAL TOLERANCES ARE: (.X) ± .06(1.5) (.XXX) ± .010(.3) (.XX) ± .005</p> <p>ANGLES ±</p>	WORK INSTRUCTION
DRAWN BY NER	REVIEW DRAWING NUMBERS	SCALE NONE
DATE 3-23-06		PART NO. UTPCHLXX**(Y) △ H
CHK'D WJC		DRAWING NO. 02479-323 SHEET 1 OR 2

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	5-13-10	BJN		H. ADDED (I) TO P/N 1. ADDED ID LABEL G. WAS CATEGORY 5E W/PANDUIT PLUGS F. ADDED T568B WIRING SCHEME E. ADDED TANGLE-FREE LATCH C. ADDED CABLE LG D. WAS PANDUIT PLUG A. ADDED SH2 B. ADDED NOTES 3-7	02479-323				
R	3-23-06	NER	WJC	RELEASED TO PRODUCTION	02479-323		RMD		





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.
 TX5e UTP LSZH PATCH CORDS

PANDUIT PART NUMBER	MIN. CABLE LENGTH
UTPCHL0.5M**Y	0.5 m
UTPCHL1M**Y	1 m
UTPCHL1.5M**Y	1.5 m
UTPCHL2M**Y	2 m
UTPCHL2.5M**Y	2.5 m
UTPCHL3M**Y	3 m
UTPCHL4M**Y	4 m
UTPCHL5M**Y	5 m
UTPCHL6M**Y	6 m
UTPCHL7M**Y	7 m
UTPCHL8M**Y	8 m
UTPCHL9M**Y	9 m
UTPCHL10M**Y	10 m
UTPCHL15M**Y	15 m
UTPCHL20M**Y	20 m
UTPCHL25M**Y	25 m
UTPCHL30M**Y	30 m
UTPCHL35M**Y	35 m
UTPCHL40M**Y	40 m



SIZE

A

DRAWING FILENAME		M02479MJ_DC323/00B	
TX5e UTP PATCH CORDS (LSZH) CUSTOMER DRAWING			
 PANDUIT ^R CORP. TINLEY PARK, IL 60477	I.I. NUMBER		
	PRODUCT SPEC		
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± .06 (1.5) (.XXX) ± .010 (.3) (.XX) ± ANGLES ±		WORK INSTRUCTION
	SCALE		NONE
DRAWN BY	REVIEW DRAWING NUMBERS		PART NO.
NER			UTPCHLXX** (Y) 
DATE			DRAWING NO.
3-23-06			02479-323
CHK'D			SHEET 2 04 2 
WJC			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	5-13-10	BJN		SEE SHEET 1 FOR REVISIONS	02479-323				