

Proxim Wireless 8 dBi Omnidirectional Antenna.

Specifications:

Electrical	
Part number	5054-OA-8
Frequency range	5470 MHz - 5875 MHz
VSWR	2.0 : 1 Max
Gain	8 dBi
Polarization	Linear, vertical
HPBW/horizontal	360 degrees
HPBW/vertical	12 degrees
Electrical downtilt	2 degrees
Power Handling	5 W (cw)
Impedance	50 ohms
Connector type	N-type Female
Mechanical	
Size	78 x 80 x 384 mm
Weight	230 g
Temperature range	-40~ +90 C
Humidity	95% @ +25 C
Survival wind speed	216 km/hr
Lightning protection	DC ground
Radome color	Gray - White
Radome material	Fiber glass

Radiation Patterns:

