DOME ENCLOSURES BRACKETS



Indoor and outdoor installations



DBH03

Ceiling bracket for DBH24 dome enclosures. It is designed to provide a cable managed solution.

DBH04

Wall bracket for DBH24 dome enclosures. It is designed to provide a cable managed solution. Compatible with corner and pole adapters.

DBH05

Bracket for DBH24 dome installation on parapet and over roofs. It is designed to provide a cable managed solution.

DPTCH1

Pole adapter compatible with DBH04 brackets.

DBHWGC

Pole adapter compatible with DBH04 brackets for DBH24 dome installation. Colour RAL9002.

DCWGH

Corner adapter compatible with DBH04 brackets.



DBH03





DBH05



DPTCH1



n	R	н	W	ıc.	1
ν	υ	П	٧V	U	L

DCWGH

AVAILABLE MODELS					
Code	Wall	Ceiling	Parapet		
	DBH04	DBH03	DBH05		
Dome enclosures					
DBH24	•	•	•		
Adapters					
DPTCH1	•				
DBHWGC	•		_		
DCWGH	•		_		

79

TECHNICAL DATA

GENERAL

Constructed from steel tube (DBH04, DCWGH, DBHWGC)

Constructed from aluminium tube (DBH03, DBH05, DPTCH1)

Epoxypolyester powder painting, black colour (white for DBHWGC)

Enclosure attachment with a single screw (DBH03 and DBH04)

MECHANICA	٨	ИE	CH	AN	ICAI	
-----------	---	----	----	----	------	--

DBH03

Internal cable management

Max load: 25kg (55lb)

Length: 922mm (36.2in)

DBH04

Internal cable management

Max load: 25kg (55lb)

Length: 357.5mm (14in)

DBH05

Installation over parapets

Internal cable management

Max load: 25kg (55lb)

Length: 812.5mm (31.9in)

DPTCH1

Pole installation

Max load: 50kg (110lb)

Pole diameters: 80 - 150mm (3.1 - 5.9in)

Compatible with DBH04

DBHWGC

Pole installation

Max load: 25kg (55lb)

Pole diameters 210mm max 225mm (8.2"- 8.85")

Colour RAL9002

Compatible with DBH04

DCWGH


Installation on corners

Max load: 50kg (110lb)


Compatible with DBH04

ENVIRONMENTS


Indoor / Outdoor




DPTCH1




DBHWGC




PACKAGE							
Code	Unit weight		Package weight		Package dimensions (WxHxL)		Master carton
	kg	lb	kg	lb	cm	in	unit
DBH03	2.0	4.4	2.6	5.7	9.0x19.5x105.5	3.5x7.7x41.5	-
DBH04	2.2	4.8	2.6	5.7	16.0x18.5x46.0	6.3x7.3x18.1	8
DBH05	5.0	11.0	6.6	14.5	7.5x51.0x76.0	2.9x20.0x29.9	-
DPTCH1	2.5	5.6	2.8	6.2	20.0x25.5x14.0	7.8x10.0x5.5	10
DCWGH	2.2	4.8	2.7	5.9	24.0x32.0x24.5	9.4x12.6x9.7	6





451



Ø 170

DBH05

DBH04

mm 1:10

82