

# Product Specifications



360-MOD-1U-24

Material ID: 760104273

SYSTIMAX 360 U/UTP Modular Panel, 24 port



- Available for use with the DYMO® labeling solution

## CHARACTERISTICS

### Dimensions

Depth, with cable management	7.25 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in

### Electrical Specifications

ANSI/TIA Category	6A
-------------------	----

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	SYSTIMAX 360™   SYSTIMAX®
Product Type	Label   Panel, modular
Color	Cool gray   Satin chrome
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	1

### Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
---------------	---

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant

**SYSTIMAX®**  
**SOLUTIONS**  
www.commscope.com

©2011 CommScope, Inc. All rights reserved.  
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.  
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2  
4/15/2011

# Product Specifications

360-MOD-1U-24 - Material ID: 760104273



ISO 9001:2008

Designed, manufactured and/or distributed under this quality management system

