

Product Specifications



VP360T-VP360T-P8X10D-L-DG

Material ID: CPCFFZ2-03

GigaSPEED® X10D VisiPatch® 360 to VisiPatch® 360 4-pair Solid Low Smoke Zero Halogen Patch Cord T, Dark Gray Jacket



CHARACTERISTICS

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	2 m 7 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Interface, connector A	VisiPatch® 360
Interface, connector B	VisiPatch® 360
Product Type	Cord
Brand	SYSTIMAX® VisiPatch® 360
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray

Product Specifications



VP360T-VP360T-P8X10D-L-DG - Material ID: CPCFFZ2-03

Package, quantity 1
Pairs, quantity 4

Mechanical Specifications

Conductor Type Solid
Material Type Copper alloy | Polycarbonate
Outlet/Module Contact Plating Gold over nickel
Plug Insertion Life, minimum 200 times
Plug Retention Force, minimum 44 N | 10 lbf
Wiring VisiPatch® 360

Wiring Diagram

	Connector A	Connector B
Position 1	Blue	Blue
Position 2	Lt. Blue	Lt. Blue
Position 3	Orange	Orange
Position 4	White/Orange	White/Orange
Position 5	Green	Green
Position 6	Lt. Green	Lt. Green
Position 7	Brown	Brown
Position 8	Lt. Brown	Lt. Brown

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



INCLUDED PRODUCTS

3095B DG 4/24 RVAR (Product Component—not orderable)
GigaSPEED® X10D 3095B Category 6A U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel