

Product Specifications



360GS10E-MGS600(WH)-L-WH

Material ID: CPCSUZ2-88

GigaSPEED® X10D 360GS10E to MGS600 on 3095B Solid Low Smoke Zero Halogen Cordage Zone Extension Cord, White Jacket, White Information Outlet



CHARACTERISTICS

Dimensions

Cord Length, maximum	100 ft 30 m
Cord Length, minimum	1 m 3 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	Information outlet
Jacket Color	White
Brand	GigaSPEED® X10D SYSTIMAX 360™ SYSTIMAX®
Information Outlet Color	White
Interface Feature, connector A	Standard

SYSTIMAX®
SOLUTIONS
www.commscope.com

©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 3
4/14/2011

Product Specifications

360GS10E-MGS600(WH)-L-WH - Material ID: CPCSUZ2-88



Interface Feature, connector B Standard

Package, quantity 1

Pairs, quantity 4

Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 30 lbf
Wiring	T568B

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



INCLUDED PRODUCTS

3095B WH 4/24 RVAR (Product Component—not orderable)

GigaSPEED® X10D 3095B Category 6A U/UTP Cable, non-plenum, white jacket, 4 pair count, variable

SYSTIMAX®
SOLUTIONS
www.commscope.com

©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 2 of 3
4/14/2011

Product Specifications

360GS10E-MGS600(WH)-L-WH - Material ID: CPCSUZ2-88



length, reel



MGS600-262

GigaSPEED® X10D MGS600 Series Information Outlet, white