

Product Specifications



110P4GS-DG

Material ID: CPC8852-03

110 to 110 2 Pair Patch Cord, Dark Gray Jacket



CHARACTERISTICS

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Interface, connector A	110 plug
Interface, connector B	110 plug
Product Type	Cord
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray
Package, quantity	1
Pairs, quantity	2

Product Specifications



110P4GS-DG - Material ID: CPC8852-03

Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	27 N 6 lbf
Wiring	110

Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	Lt. Blue
Position 2	Blue	Blue
Position 3	White/Orange	White/Orange
Position 4	Orange	Orange
Position 5		
Position 6		
Position 7		
Position 8		

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



INCLUDED PRODUCTS

1074C DG 2/24 RVAR (Product Component—not orderable)

GigaSPEED® XL 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 2 pair count, variable length, reel

5EJ2 GRAY BULK REEL (Product Component—not orderable)

DataPipe® 5EJ2 Category 5e U/UTP Cable, non-plenum, gray jacket, 2 pair count, bulk length, reel



©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

Product Specifications

110P4GS-DG - Material ID: CPC8852-03

