

Product Specifications



FAWSAUC01-JX

TeraSPEED® SC APC to Unconnectorized 0.9 mm Pigtail, Tight Buffer PVC, Yellow

CHARACTERISTICS

Construction Materials

Fiber Type	TeraSPEED®, zero water peak single-mode fiber
Total Fibers, quantity	1
Jacket Color	Yellow

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Interface, connector A	SC
Interface Feature, connector A	APC
Construction Type	Pigtail
Interface, connector B	Unterminated

Mechanical Specifications

Cable Retention Strength, maximum	0.50 lb @ 0 ° 0.50 lb @ 90 °
-----------------------------------	---------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Product Specifications

FAWSAUC01jX



INCLUDED PRODUCTS



X-TB-8W-YL-F/G

900µm Tight Buffered Fiber

- **CS-8W-TB** (Product Component—not orderable)
TeraSPEED® Singlemode Fiber
-