

# Product Specifications



FEWSCSC21-JX

TeraSPEED® SC to SC Fiber Patch Cord, 1.6 mm Simplex, Riser, Yellow Jacket

## CHARACTERISTICS

### Construction Materials

Fiber Type	TeraSPEED®, zero water peak single-mode fiber
Jacket Color	Yellow
Total Fibers, quantity	1

### Dimensions

Cord Length, maximum	999 ft   999 m
Cord Length, minimum	1 ft   1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

### Environmental Specifications

Environmental Space	Riser
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

### General Specifications

Construction Type	Simplex patch cord
Interface, connector A	SC
Interface Feature, connector A	Standard
Interface, connector B	SC
Interface Feature, connector B	Standard

### Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



# Product Specifications

FEWSCSC21JX



## INCLUDED PRODUCTS



### **R-001-SP-8W-F16YL**

1.6 mm Riser Simplex Cable

- **CS-8W-TB** (Product Component—not orderable)  
TeraSPEED® Singlemode Fiber



### **5410 001A WRYL**

1.6 mm Riser Simplex Cable

- **CS-8W-TB** (Product Component—not orderable)  
TeraSPEED® Singlemode Fiber