

# Product Specifications



FFXLCLC42-MX

LazrSPEED® 550 LC to LC Fiber Patch Cord, 1.6 mm Duplex, LSZH, Aqua Jacket



## CHARACTERISTICS

### Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Jacket Color	Aqua
Total Fibers, quantity	2

### Dimensions

Cord Length, maximum	999 ft   999 m
Cord Length, minimum	1 ft   1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

### Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

### General Specifications

Construction Type	Duplex patch cord
Interface, connector A	LC
Interface Feature, connector A	Standard
Interface, connector B	LC
Interface Feature, connector B	Standard
Ordering Note	Not available in the United States or Canada

### Mechanical Specifications

# Product Specifications

FFXLCLC42-MX



Cable Retention Strength, maximum 4.40 lb @ 90 °  
11.24 lb @ 0 °

## Regulatory Compliance/Certifications

---

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## INCLUDED PRODUCTS

**460125198** (Product Component—not orderable)  
Pre-Radiused LC Connector duplex for 1.6 mm Fiber, multimode

---