

Product Specifications



FFXLCMJ42-MX

LazrSPEED® 550 LC to MTRJ Fiber Patch Cord, 1.6 mm Duplex, LSZH, Aqua Jacket

CHARACTERISTICS

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Jacket Color	Aqua
Total Fibers, quantity	2

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Construction Type	Duplex patch cord
Interface, connector A	LC
Interface Feature, connector A	Standard
Interface, connector B	MTRJ
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



SYSTIMAX®
SOLUTIONS
www.commscope.com

©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2
5/11/2011

Product Specifications

FFXLCMJ42-MX



INCLUDED PRODUCTS

860460492 (Product Component—not orderable)

MTRJ 2 Fiber Connector for 3.0 mm Fiber, multimode, beige

460125198 (Product Component—not orderable)

Pre-Radiused LC Connector duplex for 1.6 mm Fiber, multimode
