

# Product Specifications



FJWMPMPAF-JB

TeraSPEED® MPO Female to MPO Female 24-Fiber InstaPATCH® Plus Distribution Trunk Cable, LSZH, yellow jacket

## CHARACTERISTICS

### Construction Materials

Fiber Type	TeraSPEED®, zero water peak single-mode fiber
Jacket Color	Yellow
Total Fibers, quantity	24

### Dimensions

Breakout Length	Standard
Cord Length, maximum	999 ft   999 m
Cord Length, minimum	10 ft   3 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

### Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

### General Specifications

Construction Type	InstaPATCH® Plus trunk/extension/cross-connect
Interface, connector A	MPO Female
Interface Feature, connector A	Standard
Interface, connector B	MPO Female
Interface Feature, connector B	Standard
Cable Glands	Included
Pulling Grips, quantity	0
Ordering Note	Not available in the United States or Canada

### Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

# Product Specifications

FJWMPMPAFJB



## INCLUDED PRODUCTS



**N-024-MP-8W-F12YL** (Product Component—not orderable)

Low Smoke Zero Halogen Riser MPO Trunk Cable, 24 fiber with 12 fiber subunits

- **CS-8W-MP** (Product Component—not orderable)  
TeraSPEED® Singlemode Fiber

---

**860366137** (Product Component—not orderable)

TeraSPEED® MPO Female 12 Fiber Connector, green

---