

Product Specifications



FJZMPMPAD-MB

LazrSPEED® 300 MPO Female to MPO Female 12-Fiber InstaPATCH® Plus Distribution Trunk Cable, LSZH, aqua jacket

CHARACTERISTICS

Construction Materials

Fiber Type	LazrSPEED® 300, 50 µm multimode fiber
Jacket Color	Aqua
Total Fibers, quantity	12

Dimensions

Breakout Length	Standard
Cord Length, maximum	999 ft 999 m
Cord Length, minimum	10 ft 3 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Construction Type	InstaPATCH® Plus trunk/extension/cross-connect
Interface, connector A	MPO Female
Interface Feature, connector A	Standard
Interface, connector B	MPO Female
Interface Feature, connector B	Standard
Cable Glands	Included
Pulling Grips, quantity	0
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Product Specifications

FJZMPMPAD-MB



INCLUDED PRODUCTS



N-012-MP-5L-F12AQ (Product Component—not orderable)
Low Smoke Zero Halogen Riser MPO Trunk Cable, 12 fiber

- **CS-5L-MP** (Product Component—not orderable)
LazrSPEED® 300 OM3 Multimode Fiber

860366210 (Product Component—not orderable)
LazrSPEED® Low Loss MPO Female 12 Fiber Connector, aqua
