

Product Specifications



FAXSTUC01-MX

LazrSPEED® 550 ST II to Unconnectorized 0.9 mm Pigtail, Tight Buffer PVC, Aqua

CHARACTERISTICS

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Total Fibers, quantity	1
Jacket Color	Aqua

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Interface, connector A	ST
Interface Feature, connector A	Standard
Construction Type	Pigtail
Interface, connector B	Unterminated

Mechanical Specifications

Cable Retention Strength, maximum	0.50 lb @ 0 ° 0.50 lb @ 90 °
-----------------------------------	---------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Product Specifications

FAXSTUC01-MX



INCLUDED PRODUCTS



X-TB-5K-AQ-F/G

900µm Tight Buffered Fiber

- **CS-5K-TB** (Product Component—not orderable)
LazrSPEED® 550 OM4 Multimode Fiber



MFC-STU

Pre-Radiused ST II Connector, multimode