

Product Specifications



FEWSCSC21-JX

TeraSPEED® SC to SC Fiber Patch Cord, 1.6 mm Simplex, Riser, Yellow Jacket

CHARACTERISTICS

Construction Materials

Fiber Type	TeraSPEED®, zero water peak single-mode fiber
Jacket Color	Yellow
Total Fibers, quantity	1

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Riser
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Construction Type	Simplex patch cord
Interface, connector A	SC
Interface Feature, connector A	Standard
Interface, connector B	SC
Interface Feature, connector B	Standard

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



SYSTIMAX®
SOLUTIONS
www.commscope.com

©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2
5/17/2011

Product Specifications

FEWSCSC21JX



INCLUDED PRODUCTS



R-001-SP-8W-F16YL

1.6 mm Riser Simplex Cable

- **CS-8W-TB** (Product Component—not orderable)
TeraSPEED® Singlemode Fiber



5410 001A WRYL

1.6 mm Riser Simplex Cable

- **CS-8W-TB** (Product Component—not orderable)
TeraSPEED® Singlemode Fiber