


| LOC | DIST | REVISIONS | | | | | |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| | | P | LTR | DESCRIPTION | DATE | DWN | APVD |
| E | B | | G1 | REVISED PER ECO-11-005139 | 29MAR11 | RK | HMR |

TOP VIEW




FIBER CONNECTIONS WITH BLANKING PLUG

CHASSIS MOUNT HOLES


NOTE: POWER SUPPLY IS EUP COMPLIANT

POWER INPUT SOCKET


85.0 [3.35]




REAR VIEW



SIDE VIEW




FRONT VIEW



SIDE VIEW

26.0 [1.02]



SERIAL NUMBER AND CE LABEL

FIBER SPECIFICATION LABEL

WEEE LABEL

BASE VIEW

| ITEM | QUANTITY |
|------------------|----------|
| MODULE | 1 |
| MOUNTING BRACKET | 2 |
| MOUNTING SCREW | 4 |
| POWER ADAPTER | 1 * |
| USER GUIDE | 1 |

* POWER ADAPTER IS NOT SUPPLIED WITH PART NUMBER 0-1591020-0

| PART ISSUE | PART NUMBER | COUNTRY |
|------------|-------------|---------|
| G | 0-1591020-1 | US |
| G | 0-1591020-2 | EU |
| G | 0-1591020-6 | AU |
| G | 0-1591020-7 | UK |
| G | 0-1591020-8 | IN |
| G | 0-1591020-9 | US 240V |
| G | 2-1591020-0 | AR |
| G | 6-1591020-0 | KR |
| G | 7-1591020-0 | JP |

POWER ADAPTER

STANDARD PAINT FINISH: BLACK POWDER COAT

| | | | | | |
|----------------|--|--|---------------|------------------------|--|
| DIMENSIONS: mm | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | DWN S.Lambourn 14JUN10 | |
| | | 0 PLC ± - | 1 PLC ± 0.1 | CHK P.Bickley 14JUN10 | |
| | | 2 PLC ± 0.01 | 3 PLC ± 0.001 | APVD A.Bird 14JUN10 | |
| MATERIAL - | | 4 PLC ± 0.0001 | ANGLES ± - | PRODUCT SPEC - | |
| | | FINISH - | | APPLICATION SPEC - | NAME GIGABIT ETHERNET MEDIA CONVERTER (UN-MANAGED) 1000Base-SX MULTIMODE |
| | | | | WEIGHT - | SIZE A3 |
| | | | | CUSTOMER DRAWING | CAGE CODE |
| | | | | | DRAWING NO C=1591020 |
| | | | | | SCALE NTS |
| | | | | | SHEET 1 OF 1 |
| | | | | | REV G1 |