







NOTES:

- 9 PACKAGING:
- ASSEMBLIES > 50 METER WILL BE DELIVERED ON A REEL.
  - CONNECTOR AND TAIL PROTECTION BY A SOFT PLASTIC SLEEVE ( PULL ON THIS SLEEVE IS NOT ALLOWED).
- 10 INFORMATION ABOUT A PULL AND PROTECTION KIT ASK YOUR LOCAL SALES REPRESENTATIVE.
- 11 BEFORE INSTALLING OF ALL THE CONNECTORS ALWAYS INSPECT AND CLEAN THE END FACES.

| 5                               | 2             | 2             |
|---------------------------------|---------------|---------------|
| CABLE MARKER ON LC/PC CONNECTOR | "L1" (meter)  | "L2" (meter)  |
| 1                               | 0,40 -0/+0,08 | 0,60 -0/+0,08 |
| 2                               | 0,40 -0/+0,08 | 0,60 -0/+0,08 |
| 3                               | 0,40 -0/+0,08 | 0,60 -0/+0,08 |
| 4                               | 0,40 -0/+0,08 | 0,60 -0/+0,08 |
| 5                               | 0,50 -0/+0,08 | 0,50 -0/+0,08 |
| 6                               | 0,50 -0/+0,08 | 0,50 -0/+0,08 |
| 7                               | 0,50 -0/+0,08 | 0,50 -0/+0,08 |
| 8                               | 0,50 -0/+0,08 | 0,50 -0/+0,08 |
| 9                               | 0,60 -0/+0,08 | 0,40 -0/+0,08 |
| 10                              | 0,60 -0/+0,08 | 0,40 -0/+0,08 |
| 11                              | 0,60 -0/+0,08 | 0,40 -0/+0,08 |
| 12                              | 0,60 -0/+0,08 | 0,40 -0/+0,08 |

|                                                           |             |
|-----------------------------------------------------------|-------------|
| 2 / 9 METER LENGTHS ACCORDING TO CUSTOMER DRAWING 2055705 |             |
| PART NUMBER                                               | "L" (meter) |
| X-2055725-Y                                               | XY,0        |

|                                        |  |                                                                                       |  |                                                                                 |  |
|----------------------------------------|--|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>T. VD MEULEN<br>18AUG2010                                                      |  | Tyco Electronics Tyco Electronics Nederland BV<br>'s-Hertogenbosch, Netherlands |  |
| CHK<br>T. VD MEULEN<br>18AUG2010       |  | APVD<br>M. OPPERS<br>18AUG2010                                                        |  | NAME                                                                            |  |
| DIMENSIONS:<br>mm                      |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                |  | FOBRO MM50 OM3 LEAD 12FOLD<br>LC/PC - LC/PC                                     |  |
|                                        |  | 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± -<br>FINISH |  | SIZE<br>A2                                                                      |  |
| MATERIAL<br>-                          |  | WEIGHT<br>-                                                                           |  | CAGE CODE<br>00779                                                              |  |
| CUSTOMER DRAWING                       |  |                                                                                       |  | SCALE<br>NTS                                                                    |  |
| DRAWING NO<br>C=2055725                |  |                                                                                       |  | SHEET<br>2 OF 2                                                                 |  |
| RESTRICTED TO<br>-                     |  |                                                                                       |  | REV<br>A                                                                        |  |