



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
EH	00		C	REV; EC 0B10-0154-01	18OCT01	LH	MD
			D	REV ECN 0B10-0178-02	30DEC02	LH	MD
			E	REV ECR-05-004347	09JUN05	LH	CC
			F	REV ECO-06-27719	04JAN07	LH	CD



- ONE CABLE PACKAGED IN A CLEAR POLYBAG.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS.
- DESIGNATIONS IN PARENTHESES ( ) ARE FOR REFERENCE ONLY.
- AN ALTERNATE FORM OF CONNECTOR COMPONENTS RESULTING IN EQUIVALENT PERFORMANCE IS ACCEPTABLE.



0.15	0.5	203.2 (8.00)	9-219243-8
15.24	50	15392.4 (606.00)	5-219243-0
12.20	40	12344.4 (486.00)	4-219243-0
9.15	30	9296.4 (366.00)	3-219243-0
7.62	25	7721.6 (304.00)	2-219243-5
6.10	20	6197.6 (244.00)	2-219243-0
4.88	16	4978.4 (196.00)	1-219243-6
4.57	15	4724.4 (184.00)	1-219243-5
4.27	14	4368.8 (172.00)	1-219243-4
3.66	12	3759.2 (148.00)	1-219243-2
3.35	11	3454.4 (136.00)	1-219243-1
3.05	10	3149.6 (124.00)	1-219243-0
2.74	9	2794 (110.00)	219243-9
2.44	8	2489.2 (98.00)	219243-8
2.14	7	2184.4 (86.00)	219243-7
1.83	6	1879.6 (74.00)	219243-6
1.53	5	1574.8 (62.00)	219243-5
1.22	4	1270 (50.00)	219243-4
0.92	3	965.2 (38.00)	219243-3
0.61	2	660.4 (26.00)	219243-2
0.30	1	355.6 (14.00)	219243-1
METERS, REF	FEET, REF	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. BOLES 25JUL97	Tyco Electronics Corporation Harrisburg, Pa., 17105-3608	
DIMENSIONS: MM(INCHES)		CHK B. ANTHONY 25JUL97		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. ANTHONY 25JUL97	NAME CABLE ASSEMBLY, MOD PLUG, 8 POSITION GREEN, ENHANCED CATEGORY 5	
0 PLC ± -		PRODUCT SPEC 108-1163	SIZE A2	
1 PLC ± -		APPLICATION SPEC 114-6053	CAGE CODE 00779	DRAWING NO C=219243
2 PLC ± -		WEIGHT -	RESTRICTED TO -	
3 PLC ± -		CUSTOMER DRAWING		
4 PLC ± -		SCALE NTS		
ANGLES ± -		SHEET 1 OF 1		
FINISH -		REV F		