


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006  
 © COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
1K	2		E	EC ESE0-0025-04	24Feb04	LD	JS
			F	EC ESE0-0146-04	24NOV2004	LD	JS
			G	ECR-05-005512	27JUN2005	MP	LD
			GI	Updated	12JUN2006	LD	JS

FINISHED CABLE DATA

CONDUCTORS	WIRE AWG	24 AWG Solid
	Ø RANGE in mm	0,485<=Ø<0,546
	MATERIAL	COPPER
	PLATING	BARE
	ELONGATION	15% PER EN 50288-1
INSULATION	MATERIAL	POLYETHYLENE
	OVERALL DIAMETER	1,00
DRAIN WIRE	Ø RANGE	0,4 - 0,55
	MATERIAL	COPPER
	PLATING	TINNED
	ELONGATION	15% PER EN 50288-1
BINDER	POLYESTER TAPE	OPTIONAL
INDIVIDUAL PAIR SCREEN	MATERIAL	-
OVERALL SHIELD	FOIL MATERIAL	PLASTIC LAMINATED ALUMINUM FOIL
OVERALL SHIELD	BRAID MATERIAL	-
	PLATING	-
	COVERAGE	-
	ELONGATION	-
JACKET	MATERIAL	LSZH
	OVERALL DIAMETER (D)	6,2
PULLING FORCE	MAX.	100 N

- REFER TO PRODUCT SPEC 108-93018 FOR ADDITIONAL REQUIREMENTS.
- BASENR SPECIFIC PRINT LEGEND INFO:  
AWG24 PR04 CAT5E LSZH F/UTP SOLID
- CABLE COLORED TYPES UPON REQUEST.



WHITE RAL 9010	500 m	REEL	219420-7
WHITE RAL 9010	1000 m	REEL	219420-3
WHITE RAL 9010	305 m	PULL BOX	219420-2
WHITE RAL 9010	305 m	REEL	219420-1
COLOUR	LENGTH (METRES)	PACKAGE	PART NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROVALS		TYCO ELECTRONICS	
mm		0 PLC ±-	±-	DWN	L. de Dios	24Feb04	Tyco Electronics AMP España, S.A. Barcelona, Spain.
		1 PLC ±-	±-	CHK	A. Puell	24Feb04	
		2 PLC ±-	±-	APVD	J. Sanabra	24Feb04	
MATERIAL -		3 PLC ±-	±-	PRODUCT SPEC	-		NAME
FINISH -		4 PLC ±-	±-	APPLICATION SPEC	-		CABLE, CAT5E, PR4, F/UTP, LSZH, 24AWG, SOLID
-		ANGLES ±-	±-	WEIGHT	-		SIZE
-				CUSTOMER DRAWING		SCALE	A3
-				-		SHEET	00779
-				-		OF	C=219420
-				-		REV	GI