



LOC	DIST	REVISIONS					
EH	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	REV-ECO-06-009959	01MAY06	LH	CC
			H	REV-ECO-07-016663	18JUL07	LH	JG
			J	REV ECO-07-022327	04OCT07	LH	JG



1. ONE CABLE PACKAGED IN A POLY BAG.
2. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS, CAT6.
4. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.



WIRING DIAGRAM
568B

30.48	100	30632.4 (1206.00)	9-219889-9
21.34	70	21488.4 (846.00)	7-219889-0
20.12	66	20269.2 (798.00)	6-219889-6
15.24	50	15392.4 (606.00)	5-219889-0
12.19	40	12344.4 (486.00)	4-219889-0
10.06	33	10210.8 (402.00)	3-219889-3
9.15	30	9296.4 (366.00)	3-219889-0
7.62	25	7721.6 (304.00)	2-219889-5
6.1	20	6197.6 (244.00)	2-219889-0
4.88	16	4978.4 (196.00)	1-2198889-6
4.57	15	4724.4 (184.00)	1-219889-5
4.27	14	4368.8 (172.00)	1-219889-4
3.66	12	3759.2 (148.00)	1-219889-2
3.05	10	3149.6 (124.00)	1-219889-0
2.74	9	2794 (110.00)	219889-9
2.44	8	2489.2 (98.00)	219889-8
2.14	7	2184.4 (86.00)	219889-7
1.83	6	1879.6 (74.00)	219889-6
1.53	5	1574.8 (62.00)	219889-5
1.22	4	1270 (50.00)	219889-4
0.92	3	965.2 (38.00)	219889-3
0.61	2	660.4 (26.00)	219889-2
0.30	1	355.6 (14.00)	219889-1
METERS, REF	FEET, REF	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
- 3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

2

DWN
L. SIMPSON
CHK
L. SIMPSON
APVD
L. SIMPSON
PRODUCT SPEC
APPLICATION SPEC
114-13035
WEIGHT
-

02MAR01
02MAR01
02MAR01

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
CABLE ASSEMBLY, MOD PLUG,
8 POSITION, WHITE, CAT 6
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-219889

RESTRICTED TO
-

SCALE
1:1

SHEET
1 of 1

REV
J

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 of 1

REV
J