




NOTES:


- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION
- 2 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 5 mm
- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH
INDIVIDUALLY PACKED ASSEMBLY
- 4 DAT LABEL INFO:
- UNIQUE SERIAL NUMBER
- TYCO LOGO PN
- MANUFACTURING LOCN.
- 5 BLANK LABEL
- 6 NON CROSS OVER AS PER BELOW TABLE

LEFT CONN.	RIGHT CONN.
SC CONN. A	SC CONN. B
SC CONN. B	SC CONN. A

- 7 CABLE INFO:
- CORE DIA - 50/125 μ m
- OUTER DIA - 2,5 mm
- JACKET COLOR - ORANGE
- JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349565-Y	XY,0
9-5349565-1	1,5
9-5349565-9	9,5
9-5349565-0	100 -0/+3,0

2	-	FOAC DAT-85 LABEL ON REEL	8
4	-	PROTECTIVE COVER, 2.5MM, BLACK	7
2	-	SC DUPLEX HOUSING. BEAM HALF	6
2	-	SC DUPLEX HOUSING, RET. PLATE HALF	5
4	-	SC CERAMIC, OVERMOLDED	4
4	-	CRIMP EYELET, SC, 2.0MM PLATED	3
4	-	FOAC STRAIN RELIEF, SC/FC BEIGE	2
L	-	FOCAB 2.5 50/125 DUPLEX ORANGE	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13 SEP 05 GIRIYAPPA M		 TE Connectivity			
DIMENSIONS: mm		CHK 13 SEP 05 DIWAKAR BELAVADI					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 13 SEP 05 DIWAKAR BELAVADI		NAME FOMM50 2,5mm TZ SC - SC DPX			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		—					
		—					
MATERIAL —	FINISH —	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-5349565	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE NTS	SHEET 1 of 1	REV A1