



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
EH	00		E1	REVISED PER ECO-11-005033	11MAR11	RK	HMR



1. ONE CABLE PACKAGED IN A CLEAR POLYBAG.
2. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS.
4. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
5. AN ALTERNATE FORM OF CONNECTOR COMPONENTS RESULTING IN EQUIVALENT PERFORMANCE IS ACCEPTABLE.



WIRING DIAGRAM
568A

30.48	100	30632.4 (1206.00)	9-219241-9
0.15	0.5	203.2 (8.00)	9-219241-8
27.74	91	27889.2 (1098.00)	9-219241-1
18.29	60	18440.4 (726.00)	6-219241-0
15.24	50	15392.4 (606.00)	5-219241-0
12.20	40	12344.4 (486.00)	4-219241-0
9.15	30	9296.4 (366.00)	3-219241-0
7.62	25	7721.6 (304.00)	2-219241-5
6.10	20	6197.6 (244.00)	2-219241-0
4.88	16	4978.4 (196.00)	1-219241-6
4.57	15	4724.4 (184.00)	1-219241-5
4.27	14	4368.8 (172.00)	1-219241-4
3.66	12	3759.2 (148.00)	1-219241-2
3.05	10	3149.6 (124.00)	1-219241-0
2.74	9	2794.0 (110.00)	219241-9
2.44	8	2489.2 (98.00)	219241-8
2.14	7	2184.4 (86.00)	219241-7
1.83	6	1879.6 (74.00)	219241-6
1.53	5	1574.8 (62.00)	219241-5
1.22	4	1270.0 (50.00)	219241-4
0.92	3	965.2 (38.00)	219241-3
0.61	2	660.4 (26.00)	219241-2
0.30	1	355.6 (14.00)	219241-1
METERS, REF	FEET, REF	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
M. BOLES
25JUL97

CHK
B. ANTHONY
25JUL01

APVD
B. ANTHONY
25JUL97

PRODUCT SPEC
108-1163

APPLICATION SPEC
114-6053

MATERIAL
-

FINISH
-

TE Connectivity

CABLE ASSEMBLY, MOD PLUG, 8 POSITION
GRAY, ENHANCED CATEGORY 5

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-219241

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
E1