


LOC	DIST	REVISIONS			
H	—	P	LTR	DESCRIPTION	DATE
		A		INITIAL RELEASE	01 SEP 05

DWN	APVD
RC	JE



NOTES:

1. INSERTION LOSS $\leq$ 0,75dB, RANDOM MATED
2. RETURN LOSS $\geq$ 35dB, RANDOM MATED
3. FILLED OUT TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
4. NON-CROSS OVER AS PER TABLE

FIBER COLOUR	LEFT CONN.
BLUE	A
RED	B

5. CABLE INFO:
- CORE DIAMETER: 9/125 μ m

— OUTER BUFFER DIAMETER: 235–255 μ m

— OUTER BUFFER COLOUR: BLUE & RED

— OUTER BUFFER MATERIAL: UV CURED ACRYLATE

PART NUMBER	”L” (meter)	”L1” 0.9 TUBE (meter)
0–6391366–1	3,0 –0/+0,1	2,5 –0/+0,05
0–6391366–2	2,0 –0/+0,1	1,5 –0/+0,05

1	—	JACK PLUG DUST CAP	10
1	—	JACK HOUSING, BLUE	9
1	—	MINI–MT FERRULE, SM	8
1	—	PIN KEEPER WITH PINS SM MTRJ	7
1	—	SPRING	6
1	—	SPRINGPUSH ROUND	5
1	—	BOOT BARE BUFFER, BLACK	4
L1	—	0,9 TUBING, THIN WALL, CLEAR 2,5m	3
L	—	FOCAB 9/125 BARE FIBER, RED	2
L	—	FOCAB 9/125 BARE FIBER, BLUE	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 01 SEP 05	tyco Electronics Tyco Electronics Nederland BV 's–Hertogenbosch, Netherlands	
		CHK A. HENGELMOLEN 01 SEP 05		
		APVD J. ELENBAAS 01 SEP 05	NAME	
DIMENSIONS: mm		PRODUCT SPEC	FOSM PIGTAIL 0.9 2xBARE FIBER MT–RJ JACK	
		APPLICATION SPEC		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT	SIZE A2	CAGE CODE 00779
MATERIAL		CUSTOMER DRAWING	DRAWING NO C=6391366	RESTRICTED TO
		SCALE NTS	SHEET 1 OF 1	REV A