


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
IJ	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D1		ECR 11-001125	17 JAN 11	MO	MO



NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
 CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION
- △ INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 5 mm
- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- △ DAT LABEL INFO:
 - UNIQUE SERIAL NUMBER
 - TYCO LOGO PN
 - MANUFACTURING LOCN.
- △ BLANK LABEL
- 6 NON CROSS OVER AS PER BELOW TABLE

LEFT CONN.	RIGHT CONN.
SC CONN. A	SC CONN. B
SC CONN. B	SC CONN. A

7 CABLE INFO:
 CORE DIA - 50/125 μ m
 OUTER DIA - 2,5 mm
 JACKET COLOR - AQUA
 JACKET MATERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-6536464-Y	XY,0
8-6536464-1	0,6
9-6536464-1	1,5
9-6536464-2	2,5
9-6536464-3	3,5
9-6536464-4	4,5
9-6536464-9	9,5

2	-	FOAC DAT-85 LABEL	8
4	-	PROTECTIVE COVER, 2.5MM, BLACK	7
2	-	SC DUPLEX HOUSING. BEAM HALF	6
2	-	SC DUPLEX HOUSING, RET. PLATE HALF	5
4	-	SC CERAMIC, OVERMOLDED	4
4	-	CRIMP EYELET, SC, 2.0MM PLATED	3
4	-	FOAC STRAIN RELIEF, SC/FC BEIGE	2
L	-	FOCAB 50/125 TZ 2.5S OM3 AQUA	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16 DEC 05 GIRIYAPPA M	Tyco Electronics Corporation Tyco Electronics Corporation FOBU, Bangalore, India	
DIMENSIONS: mm		CHK 16 DEC 05 DIWAKAR BELAVADI	NAME -	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 16 DEC 05 DIWAKAR BELAVADI	PRODUCT SPEC -	
0 PLC ± -		APPLICATION SPEC -		
1 PLC ± -		WEIGHT -		
2 PLC ± -		SCALE A2 00779 C=6536464		
3 PLC ± -		SHEET 1 OF 1		
4 PLC ± -		REV D1		
ANGLES ± -		RESTRICTED TO -		
FINISH -		CUSTOMER DRAWING		

6536464