


D

C

B

A



LC CLIP SIDE MARK	SC CONN. MARK
A	B
B	A

NOTES:

- 1ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm I.E.C. 61300-3-4 METHOD B
- 2RETURN LOSS ≥ 30 dB, IN MATED CONDITION
- 3FILLED OUT TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- 4BLANK LABEL
- 5CABLE INFORMATION:

— CORE DIAMETER:

50/125 μm

— OUTER JACKET DIAMETER:

1.8x3.6 mm


— OUTER JACKET COLOUR:

AQUA

— OUTER JACKET MATERIAL:

LSZH
- 6FOR LENGTHS < 60 cm SHORTER SLIT LENGTHS APPLY
- 7SC DUPLEX CONNECTOR IS LEFT UNASSEMBLED AS SHOWN
- 8INDIVIDUAL LENGTH DIFFERENCE ON SC SIDE ≤ 5 mm
- 9ADDITIONAL ATTENUATION FOR LONG LEADS ACC. TO CUSTOMER DRAWING 1920435
- 10DELIVERED ON A REEL IN A BOX

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-6536967-Y	XY.0
8-6536967-1	1.5 -0/+0.1
8-6536967-2	100.0 -0/+3.0
9-6536967-0	0.5 -0/+0.05
9-6536967-1	0.75 -0/+0.1
9-6536967-2	2.5 -0/+0.1

2	BLANK LABEL		4
1	SC DUPLEX CONNECTOR, MULTI MODE		3
1	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE		2
L	FOCAB 1.8MZ OM3 50/125, AQUA LSZH		1
Qty	Description		Item
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING R. COOLEN A. HENGELMOLEN A. HENGELMOLEN — — — — Tyco Electronics Tyco Electronics Corporation 's-Hertogenbosch, Nederland NAME FOMM50 OM3 LEAD 1.8MZ LC DUPLEX – SC DUPLEX SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C=6536967 —
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH ± ± ± ± ± ± —	
			
MATERIAL —			