


D

C

B

A



LC CLIP SIDE MARK		LC CLIP SIDE MARK
A	↔	B
B	↔	A

NOTES:

- 1ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm I.E.C. 61300-3-4 METHOD B
- 2RETURN LOSS ≥ 30 dB, IN MATED CONDITION
- 3FILLED OUT TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- △4BLANK LABEL
- 5CABLE INFORMATION:

- CORE DIAMETER:50/125 μm

- OUTER JACKET DIAMETER:1.8x3.6 mm

- OUTER JACKET COLOUR:AQUA

- OUTER JACKET MATERIAL:LSZH
- △6FOR LENGTHS < 60 cm SHORTER SLIT LENGTHS APPLY

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-6536969-Y	XY.0
8-6536969-1	1.5 -0/+0.1
8-6536969-2	2.5 -0/+0.1
8-6536969-3	3.5 -0/+0.1
8-6536969-4	100.0 -0/+3.0
9-6536969-0	0.5 -0/+0.1
9-6536969-1	0.75 -0/+0.1
9-6536969-2	0.2 -0/+0.03

2	BLANK LABEL	3			
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2			
L	FOCAB 1.8MZ OM3 50/125, AQUA LSZH	1			
Qty	Description	Item			
THIS DRAWING IS A CONTROLLED DOCUMENT.					
DWN R. COOLEN 01AUG2007		 Tyco Electronics Corporation 's-Hertogenbosch, Nederland			
CHK A. HENGELMOLEN 01AUG2007					
APVD A. HENGELMOLEN 01AUG2007					
PRODUCT SPEC					
APPLICATION SPEC		NAME FOMM50 OM3 LEAD 1.8MZ LC DUPLEX - LC DUPLEX			
MATERIAL					
WEIGHT					
CUSTOMER DRAWING					
DIMENSIONS: mm		SIZE A2	CAGE CODE 00779	DRAWING NO C-6536969	RESTRICTED TO —
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE NTS			
0 PLC ± -		SHEET 1 of 1			
1 PLC ± -		REV G			
2 PLC ± -					
3 PLC ± -					
4 PLC ± -					
ANGLES ± -					
FINISH					
—					