

Structural Hardware

Modular OF Splicing Outlet 45X45 for 2 Snap-in adaptors

Nexans ref.: N420.035

- For all 45x45mm fittings
- Fits Surface Mount Boxes, Cover plates and Ducts
- Outlets include labeling and shutters
- Suitable for all snap-in adaptors.
- Easy click-in mechanism.

Description

Splicing Telecom Outlet designed for robust Fibre To The Desk Applications. The outlet combines the benefits of Nexans Snap-in concept with full flexibility of termination methods: direct, splicing with aluminium protections and splicing with heat shrink protections. Up to 4 fibres in 1 outlet!

Compatibility

Designed for Nexans snap-in adapters:

Simplex SC Singlemode - Multimode

Duplex SC Single Mode - Multimode

Duplex LC Single mode - Multi Mode

MT-RJ Multimode

The outlet is also compatible with all copper snap-in! (cat5-cat6-Cat7)

By using euromod adaptor (N800.375), the outlet fits 50x50 footprints

**LANmark-OF**

Standards

International ISO/IEC 11801

Splice holders

4x1 Aluminium protection

4x1 Heat Shrink protection

Technical Specifications

Material: PC ABS

UL listed: UL94V0

Color: White

Weight: 80g

Dimensions: 74x125x34 (including clips 45x45)

Installation

The outlet can be installed directly in ducts, with cover plates or on surface mount boxes. 2 cover positions have been designed to best meet current structural hardware products available in the market.