

- Hand Reamer
- Handreibahle
- Handruimer
- Alésoir à main
- Escariador de mano
- Mandril Manual



B100

d2=d1 with tolerance e9 / d2=d1 mit Toleranz e9 / d2=d1 met tolerantie e9 / d2=d1 en tolérance e9 / d2=d1 con tolerancia e9 / d2=d1
tolerância e9



■	1.1	1.2	1.3	1.4	2.1	3.1	4.1	6.2									
●	1.5	1.6	3.2	3.3	3.4	4.2	4.3	5.1	5.2	5.3	6.1	6.3	6.4	7.1	7.2	8.2	

d ₁ Ø Inch	d ₁ Ø mm	l ₁ mm	l ₂ mm	z	a mm	e-Code
1/16	1.50	41	20	3	1.12	B1001.5
	1.59	41	20	3	1.12	B1001/16
	1.60	44	21	3	1.25	B1001.6
5/64	1.98	47	23	4	1.40	B1005/64
	2.00	50	25	4	1.60	B1002.0
3/32	2.38	54	27	4	1.80	B1003/32
	2.50	58	29	4	2.10	B1002.5
7/64	2.78	62	31	6	2.10	B1007/64
	3.00	62	31	6	2.40	B1003.0
1/8	3.18	66	33	6	2.40	B1001/8
	3.20	66	33	6	2.40	B1003.2
	3.50	71	35	6	2.70	B1003.5
9/64	3.57	71	35	6	2.70	B1009/64
5/32	3.97	76	38	6	3.00	B1005/32
	4.00	76	38	6	3.00	B1004.0
11/64	4.37	81	41	6	3.40	B10011/64
	4.50	81	41	6	3.40	B1004.5
3/16	4.76	87	44	6	3.80	B1003/16
	5.00	87	44	6	3.80	B1005.0
13/64	5.16	87	44	6	3.80	B10013/64
	5.50	93	47	6	4.30	B1005.5
7/32	5.56	93	47	6	4.30	B1007/32
15/64	5.95	93	47	6	4.90	B10015/64
	6.00	93	47	6	4.90	B1006.0
1/4	6.35	100	50	6	4.90	B1001/4
	6.50	100	50	6	4.90	B1006.5
17/64	6.75	107	54	6	5.50	B10017/64
	7.00	107	54	6	5.50	B1007.0
9/32	7.14	107	54	6	6.20	B1009/32
	7.50	107	54	6	6.20	B1007.5
19/64	7.54	115	58	6	6.20	B10019/64
5/16	7.94	115	58	6	6.20	B1005/16
	8.00	115	58	6	6.20	B1008.0
21/64	8.33	115	58	6	7.00	B10021/64
	8.50	115	58	6	7.00	B1008.5
11/32	8.73	124	62	6	7.00	B10011/32
	9.00	124	62	6	7.00	B1009.0
23/64	9.13	124	62	6	8.00	B10023/64
	9.50	124	62	6	8.00	B1009.5
3/8	9.53	124	62	6	8.00	B1003/8
25/64	9.92	133	66	6	8.00	B10025/64
	10.00	133	66	6	8.00	B10010.0
13/32	10.32	133	66	6	8.00	B10013/32
	10.50	133	66	6	8.00	B10010.5
	11.00	142	71	6	9.00	B10011.0
7/16	11.11	142	71	6	9.00	B1007/16

d ₁ Ø Inch	d ₁ Ø mm	l ₁ mm	l ₂ mm	z	a mm	e-Code
	11.50	142	71	6	9.00	B10011.5
	12.00	152	76	6	9.00	B10012.0
	12.50	152	76	6	10.00	B10012.5
1/2	12.70	152	76	6	10.00	B1001/2
	13.00	152	76	6	10.00	B10013.0
17/32	13.49	163	81	8	11.00	B10017/32
	13.50	163	81	8	11.00	B10013.5
	14.00	163	81	8	11.00	B10014.0
9/16	14.29	163	81	8	11.00	B1009/16
	14.50	163	81	8	11.00	B10014.5
	15.00	163	81	8	12.00	B10015.0
19/32	15.08	163	81	8	12.00	B10019/32
5/8	15.88	175	87	8	12.00	B1005/8
	16.00	175	87	8	12.00	B10016.0
	17.00	175	87	8	13.00	B10017.0
11/16	17.46	188	93	8	14.50	B10011/16
	18.00	188	93	8	14.50	B10018.0
	19.00	188	93	8	14.50	B10019.0
3/4	19.05	188	93	8	14.50	B1003/4
	20.00	201	100	8	16.00	B10020.0
13/16	20.64	201	100	8	16.00	B10013/16
	21.00	201	100	8	16.00	B10021.0
	22.00	215	107	8	18.00	B10022.0
7/8	22.23	215	107	8	18.00	B1007/8
	23.00	215	107	8	18.00	B10023.0
	24.00	231	115	8	18.00	B10024.0
	25.00	231	115	8	20.00	B10025.0
1"	25.40	231	115	8	20.00	B1001
	26.00	231	115	8	20.00	B10026.0
	27.00	247	124	10	22.00	B10027.0
	28.00	247	124	10	22.00	B10028.0
	29.00	247	124	10	22.00	B10029.0
	30.00	247	124	10	24.00	B10030.0
	31.00	265	133	10	24.00	B10031.0
	32.00	265	133	10	24.00	B10032.0
	33.00	265	133	10	26.00	B10033.0
	34.00	284	142	10	26.00	B10034.0
	35.00	284	142	10	29.00	B10035.0
	36.00	284	142	10	29.00	B10036.0
	37.00	284	142	10	29.00	B10037.0
	38.00	305	152	10	29.00	B10038.0
	39.00	305	152	10	32.00	B10039.0
	40.00	305	152	10	32.00	B10040.0
	45.00	326	163	12	35.00	B10045.0
	50.00	347	174	12	39.00	B10050.0