

1505A Coax - RG-59/U Type



For more Information
please call

1-800-Belden1



Description:

20 AWG solid .032" bare copper conductor, gas-injected foam HDPE insulation, Duofoil® + tinned copper braid shield (95% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	Solid	BC - Bare Copper	.032

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.145

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.233 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 31 lbs/1000 ft.

Max. Recommended Pulling Tension: 47 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: 59/U

Flame Test

UL Flame Test: UL1666 Vertical Shaft

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes - Black only

Suitability - Aerial: Yes - Black only, when supported by a messenger wire

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 1506A

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/ft)

0.107

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.3

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/ft)

1.22

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

10.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.8

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1.000 0.300

3.600 0.600

5.000 0.630

6.000 0.690

7.000 0.740

10.000 0.900

12.000 0.910

25.000 1.300

67.500 2.050

71.500 2.100

88.500 2.200

100.000 2.300

135.000 2.700

143.000 2.800

180.000	3.100
270.000	3.800
360.000	4.400
540.000	5.500
720.000	6.400
750.000	6.500
1000.000	7.600
1500.000	9.300
2000.000	10.900
3000.000	13.400
2250.000	11.600
4500.000	16.400

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination. 75 +/- 1.5 Ohms

Other Electrical Characteristic 2: Return Loss tested in accordance with ASTM D-4566 paragraph 45.3, using a 75 Ohm fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5	1600	23
1600	4500	21

Sweep Test

Sweep Testing: 100% Sweep tested 5 MHz to 4.5 GHz.

Misc. Information (Overall)

Notes (Overall)

Notes: Also available in bundled versions. See 7794A through 7798A.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1505A N3U1000	1,000 FT	35.000 LB	GREEN, MIL	C	#20 PE/GIFHDPE SH FR PVC
1505A N3U5000	5,000 FT	165.000 LB	GREEN, MIL	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0011000	1,000 FT	35.000 LB	BROWN	C	#20 PE/GIFHDPE SH FR PVC
1505A 0015000	5,000 FT	165.000 LB	BROWN	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0021000	1,000 FT	35.000 LB	RED	C	#20 PE/GIFHDPE SH FR PVC
1505A 002500	500 FT	15.500 LB	RED	C	#20 PE/GIFHDPE SH FR PVC
1505A 0025000	5,000 FT	165.000 LB	ORANGE	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0031000	1,000 FT	35.000 LB	ORANGE	C	#20 PE/GIFHDPE SH FR PVC
1505A 0035000	5,000 FT	165.000 LB	ORANGE	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0041000	1,000 FT	35.000 LB	YELLOW	C	#20 PE/GIFHDPE SH FR PVC
1505A 0045000	5,000 FT	165.000 LB	YELLOW	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0061000	1,000 FT	35.000 LB	BLUE, LIGHT	C	#20 PE/GIFHDPE SH FR PVC
1505A 006500	500 FT	15.500 LB	BLUE, LIGHT	C	#20 PE/GIFHDPE SH FR PVC
1505A 0065000	5,000 FT	165.000 LB	BLUE, LIGHT	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0071000	1,000 FT	35.000 LB	VIOLET	C	#20 PE/GIFHDPE SH FR PVC
1505A 0075000	5,000 FT	165.000 LB	VIOLET	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0081000	1,000 FT	35.000 LB	GRAY	C	#20 PE/GIFHDPE SH FR PVC
1505A 0085000	5,000 FT	165.000 LB	GRAY	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0091000	1,000 FT	35.000 LB	WHITE	C	#20 PE/GIFHDPE SH FR PVC
1505A 0095000	5,000 FT	165.000 LB	WHITE	C N	#20 PE/GIFHDPE SH FR PVC
1505A 0101000	1,000 FT	35.000 LB	BLACK	C	#20 PE/GIFHDPE SH FR PVC

1505A 010500	500 FT	17.500 LB	BLACK	C	#20 PE/GIFHDPE SH FR PVC
1505A 0105000	5,000 FT	165.000 LB	BLACK	C N	#20 PE/GIFHDPE SH FR PVC

Notes:

C = CRATE REEL PUT-UP.

N = FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

Revision Number: 6 Revision Date: 09-30-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.