

2413 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables



For more Information
please call

1-800-Belden1

**Description:**

23 AWG Solid Bare Copper Conductors, Dual FRPO/FEP Insulation, Tape Separator, Ripcord, Flamarrest® Jacket.

Usage (Overall)**Suitable Applications:**

Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG
ANYLAN, 155 ATM, 622 ATM, 250MHz Category 6

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Insulation**Insulation Material:**

Insulation Material
FRPO/FEP - Flame Retardant Polyolefin/Fluorinated Ethylene Propylene

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.225

Outer Jacket Ripcord:

Yes

Overall Cable**Overall Cabling Separator Material:**

Dielectric Tape

Overall Nominal Diameter:

0.225 in.

Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)**Storage Temperature Range:**

-20°C To +75°C

Installation Temperature Range:

+5°C To +50°C

2413 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables

Operating Temperature Range:	0°C To +75°C
------------------------------	--------------

Bulk Cable Weight:	27 lbs/1000 ft.
--------------------	-----------------

Max. Recommended Pulling Tension:	40 lbs.
-----------------------------------	---------

Min. Bend Radius (Install)/Minor Axis:	1 in.
--	-------

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMP
-------------------------	-----

CEC/C(UL) Specification:	CMP
--------------------------	-----

Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class E
------------------	-------------------------------------

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	10/13/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Telecommunications Standards:	Category 6 - TIA 568.C.2
-------------------------------	--------------------------

Other Specification:	Third party verified to Category 6
----------------------	------------------------------------

Applicable Patents:

Country	Patent
US	5563377
US	6570095
US	6998537
US	7179999
CANADA	2144694
US	7977575

Flame Test

UL Flame Test:	NFPA 262 Plenum Flame Test (UL910)(FT6)
----------------	---

C(UL) Flame Test:	FT6
-------------------	-----

CSA Flame Test:	FT6
-----------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	No
------------------------	----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Non-Plenum Number:	2412
--------------------	------

Electrical Characteristics (Overall)**Nom. Mutual Capacitance:**

Capacitance (pF/ft)
15

Maximum Capacitance Unbalance:

Capacitance (pF/ft)
330.000

Maximum Capacitance Unbalance (pF/100 m):	330
---	-----

Nominal Velocity of Propagation:

2413 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables

VP (%)

72

Maximum Delay:

Delay (ns/100 m)

537 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)

45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

8.2

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

5

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
0.772	1.800	77.0	75.0	75.2	73.2	
1	2.000	75.3	73.3	73.3	71.3	20.000
4	3.700	66.3	64.3	62.6	60.6	23.000
8	5.200	63.3	61.3	58.1	56.1	24.500
10	5.800	61.8	59.8	56.0	54.0	25.000
16	7.400	58.6	56.6	51.2	49.2	25.000
20	8.300	57.1	55.1	48.8	46.8	25.000
25	9.300	55.5	53.5	46.3	44.3	24.300
31.25	10.400	54.0	52.0	43.6	41.6	23.600
62.5	15.000	49.1	47.1	34.1	32.1	21.500
100	19.300	45.8	43.8	26.5	24.5	20.800
155	24.500	42.7	40.7	18.2	16.2	19.500
200	28.300	40.9	38.9	12.6	10.6	18.700
250	32.100	39.3	37.3	7.2	5.2	18.000
300	35.600	38.1	36.1	2.5	-0.5	17.500
350	38.900	37.1	35.1	-1.7	-3.7	17.000
400	42.000	36.3	34.3	-5.7	-7.7	16.600
450	45.000	35.5	33.5	-9.5	-11.5	16.200
500	47.900	34.8	32.8	-13.0	-15.0	15.900
550	50.600	34.2	32.2	-16.4	-18.4	15.600

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
0.772	100 ± 15	102 ± 15	73.0	70.0
1	100 ± 15	100 ± 15	70.8	67.8
4	100 ± 15	100 ± 15	58.8	55.8
8	100 ± 15	100 ± 15	52.7	49.7
10	100 ± 15	100 ± 15	50.8	47.8
16	100 ± 15	100 ± 15	46.7	43.7
20	100 ± 15	100 ± 15	44.8	41.8
25	100 ± 15	100 ± 15	42.8	39.8
31.25	100 ± 15	100 ± 15	40.9	37.9
62.5	100 ± 15	100 ± 15	34.9	31.9
100	100 ± 15	100 ± 15	30.8	27.8
155	100 ± 22	100 ± 15	27.0	24.0
200	100 ± 22	100 ± 15	24.8	21.8
250	100 ± 32	100 ± 15	22.8	19.8

2413 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables

300	100 ± 32	100 ± 15	21.3	18.3
350			19.9	16.9
400			18.8	15.8
450			17.7	14.7
500			16.8	13.8
550			16.0	13.0

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft./1m intervals. Third party verified to ANSI/TIA-568-C.2, Category 6. Values above 300 MHz are for Engineering Information Only.

Reference (Overall)**Previous Part Number:**

24567415, 24567715, 24567736T, 24567615T, 25067545, 25067545T, 25067515T, 24567745T, 24567715T, 25067845, 25067845T, 25067836, 25067836T, 24567815, 24567815T, 2456705T, 24567145, 24567145T, 24567115, 24567115T, 24567345, 24567345T, 24567336, 24567336T, 24567315, 24567315T, 24567445T, 24567436, 24567436T, 24567415T, 24567A15T, 24567945, 24567945T, 24567936T, 24567915, 24567915T

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
2413 D15A1000	1,000 FT	31.000 LB	BLUE		CAT6+ 4PR U/UTP CMP RIB
2413 D15U1000	1,000 FT	29.000 IN	BLUE		CAT6+ 4PR U/UTP CMP BOX
2413 D151000	1,000 FT	28.000 LB	BLUE		CAT6+ 4PR U/UTP CMP REEL
2413 D152500	2,500 FT	67.500 LB	BLUE		CAT6+ 4PR U/UTP CMP REEL
2413 003A1000	1,000 FT	34.000 LB	ORANGE		CAT6+ 4PR U/UTP CMP RIB
2413 0031000	1,000 FT	32.000 LB	ORANGE		CAT6+ 4PR U/UTP CMP REEL
2413 004A1000	1,000 FT	34.000 LB	YELLOW		CAT6+ 4PR U/UTP CMP RIB
2413 0041000	1,000 FT	32.000 LB	YELLOW		CAT6+ 4PR U/UTP CMP REEL
2413 0042500	2,500 FT	75.000 LB	YELLOW		CAT6+ 4PR U/UTP CMP REEL
2413 005A1000	1,000 FT	34.000 FT	GREEN, DARK		CAT6+ 4PR U/UTP CMP RIB
2413 0052500	2,500 FT	75.000 LB	GREEN, DARK		CAT6+ 4PR U/UTP CMP REEL
2413 007A1000	1,000 FT	34.000 FT	VIOLET		CAT6+ 4PR U/UTP CMP RIB
2413 008A1000	1,000 FT	34.000 LB	GRAY		CAT6+ 4PR U/UTP CMP RIB
2413 008U1000	1,000 FT	28.000 IN	GRAY		CAT6+ 4PR U/UTP CMP BOX
2413 0081000	1,000 FT	32.000 LB	GRAY		CAT6+ 4PR U/UTP CMP REEL
2413 009A1000	1,000 FT	34.000 LB	WHITE		CAT6+ 4PR U/UTP CMP RIB
2413 009U1000	1,000 FT	28.000 IN	WHITE		CAT6+ 4PR U/UTP CMP BOX
2413 0091000	1,000 FT	32.000 LB	WHITE		CAT6+ 4PR U/UTP CMP REEL
2413 0092500	2,500 FT	75.000 LB	WHITE		CAT6+ 4PR U/UTP CMP REEL
2413 010A1000	1,000 FT	34.000 FT	BLACK		CAT6+ 4PR U/UTP CMP RIB
2413 0102500	2,500 FT	75.000 LB	BLACK		CAT6+ 4PR U/UTP CMP REEL
2413 012A1000	1,000 FT	34.000 LB	PINK		CAT6+ 4PR U/UTP CMP RIB

Revision Number: 6 Revision Date: 09-29-2011

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and

2413 Multi-Conductor - Enhanced Category 6 Nonbonded-Pair Cables

the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.