



AX100495 Panels - FiberExpress Wall Mount Patch Panel - Small Wall Mount



For more Information
please call

1-800-Belden1

Description:

FiberExpress Patch Panel, Small Wall Mount, Black.

Usage (Overall)

Suitable Applications: FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room

Related Parts: FiberExpress Adapter Strips, Fiber Splice Organizer Trays and Kits

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity: 2 Strips; 24 Fibers (SC, SCD, ST, FC); 48 Fibers (LCD, MT-RJ). One 8-inch splice tray kit (A0649869)

Access

Front Connection: Flush

Dimensions**Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
10.400	15.400	3.400

Materials**Materials:**

Description	Material
Panel	Steel
LH Door	Steel
RH Door	Lexan

Color

Color: Black

Weight

Weight: 5.950 lbs.

Included Parts

Included Parts: 6 Wood Screws (#10x1inch); 2 Velcro Strap; 9 Tie Wrap; 1 Admin Label; 1 Caution Label, 1 Installation Manual

Packaging

Packaging: Individually packaged in a cardboard box.

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +70°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Suitability**

Suitability - Indoor: Yes

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX101059 included with the product or visit our web site at <http://www.belden.com>

Product Family**Part Numbers:**

Description	Item Number
-------------	-------------

AX100495 Panels - FiberExpress Wall Mount Patch Panel - Small Wall Mount

FiberExpress Wall Mount PP, Small, Black	AX100495
FiberExpress Wall Mount PP, Medium, Black	AX100540
FiberExpress Wall Mount PP, Large, Black	AX100542

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX100495	1 EA	17.590 LB			FIB EXPRESS WLMNT 12/24

Revision Number: 0 Revision Date: 05-28-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.