


AX102307 Modular Connectors - FX Manager Connector Module , MPO(m)- LC type, 24 Pre-Terminated



For more Information
please call

1-800-Belden1



Description:

FiberExpress Manager Connector Module , Zirconia-Ceramic , Single-mode (OS2), MPO(m) - LC type, 24 Pre-Terminated

Usage (Overall)

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, DataCenters
Related Parts:	FiberExpress Manager: Shelf and 1U Rack Mount Patch Panel. Flex Kit, Splice Holder Kit

Physical Characteristics (Connectivity)

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
5.700	1.100	9.600

Materials

Materials:

Description	Type	Material	Color
Module Holder		Plastic - UL94V-0	
Front Connector Body	LC	Plastic - UL94V-0	Blue
Adapter Sleeve		Zirconia-Ceramic	
Rear Connector Body	MPO Female	Plastic - UL94V-0	Black

Color

Color: Gray

Weight

Weight: 0.500 lbs.

Included Parts

Included Parts: Dust Caps

Packaging

Packaging: Individually packaged in a plastic bag, Shipped in cardboard box

Mechanical Characteristics (Connectivity)

Termination Interface:

Termination	Connection	Durabilities
Front	Mated Connection	500 cycles
Rear	Mated Connection	xx cycles

Connector/Hardware Retention: 11.250 lbs.

Plug/Connector Retention: 11.250 lbs.

Storage Temperature Range: -40°C To +75°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AX102307 Modular Connectors - FX Manager Connector Module , MPO(m)- LC type, 24 Pre-Terminated

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

MII Order #39 (China RoHS): EUP 50

Telecommunications Standards: TIA 568.C.3

Safety Listing: ACA

Suitability

Suitability - Indoor: Yes - Indoor

Transmission Characteristics (Connectivity)**Transmission Specifications:**

Product Description	Multimode insertion lost (max dB)	Multimode Reflectance (dB)	Single-Mode insertion lost (max dB)	Single-Mode Reflectance (dB)
FiberExpress Connector Module Pre-terminated MPO-ST Type	1.50	< -20	1.25	< -55
FiberExpress Connector Module Pre-terminated MPO- SC Duplex	1.50	< -20	1.25	< -55
FiberExpress Connector Module Pre-terminated MPO-MT-RJ	1.40	< -20	1.40	< -45
FiberExpress Connector Module Pre-terminated MPO-LC Duplex	1.15	< -20	1.15	< -50

Notes (Overall)Notes: For additional about this product, visit our web site at <http://www.belden.com>.**Product Family****Part Number List:**

Description	Multimode	Single-Mode
ST type 6 fibers	AX101089	AX100936
ST type 12 fibers	AX101187	AX101186
SC Simplex 6 fibers	-	AX100943
SC Duplex 6 fibers	AX101092	AX100944
SC Duplex (ST in) 12 fibers	AX101120	AX101119
SC Duplex 12 UPC pigtails	-	AX101715
SC Duplex 12 fibers	AX101714	AX101713
LC Duplex 8 fibers	AX101621	AX101620
LC Duplex 12 fibers	AX101528	AX101527
LC Duplex 12 fibers (OM3-AQUA)	AX103071	-
LC Duplex 24 fibers	AX102306	AX102305
LC Duplex 24 fibers (OM3-AQUA)	AX103070	-
MT-RJ 12 fibers	AX101096	AX101581
FC Single-mode/Multimode 6 fibers	-	AX100937
FC Single-mode/Multimode 8 fibers	-	AX101482

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102307	1 EA	0.000 LB			FXM MODULE 24-FIBER

Revision Number: 0 Revision Date: 06-19-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or

AX102307 Modular Connectors - FX Manager Connector Module , MPO(m)- LC type, 24 Pre-Terminated

exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.
Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.