

## AX102903 Panels - KeyConnect Video F Coax, Recessed



For more Information  
please call

1-800-Belden1

**Description:**

KeyConnect Video F, Coax, Recessed

**Usage (Overall)**

Suitable Applications: - Coax

Related Parts: - Compatible KeyConnect-style Faceplate and Patch Panel

**Physical Characteristics (Connectivity)****Access**

Front Connection: Recessed

**Dimensions****Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
0.870	0.640	0.870

**Materials****Materials:**

Description	Material
Insert	Plastic - UL94V-0

**Color**

Color: Almond

**Weight**

Weight: 0.033 lbs.

**Packaging**

Packaging: 10 units packaged in a plastic bag.

**Mechanical Characteristics (Connectivity)**

Footprint/Type: KeyConnect

Connector/Hardware Retention: 20 lbs.

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -10°C To +60°C

Operating Temperature Range: -10°C To +60°C

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

MII Order #39 (China RoHS): Yes

Safety Listing: Bi-national (UL/CSA) Standard Listed

**Suitability**

Suitability - Indoor: Yes

## AX102903 Panels - KeyConnect Video F Coax, Recessed

## Transmission Characteristics (Connectivity)

## Notes (Overall)

**Notes:** For proper installation refer to Installation Guide PX103826. Visit our web site at <http://www.belden.com>

## Product Family

## Part Numbers:

Item Number	Color
AX102903	Almond
AX102904	Elec. White
AX102905	Black

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102903	1 EA	0.033 LB			KEYSTONE F COAX RECESSED

Revision Number: 0    Revision Date: 06-03-2009

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.