



## Control 2 to 8 PCs from one keyboard, monitor, and mouse

### CompuSwitch

Connect any mix of PCs (PS/2® or AT), Sun®, and Mac®, running any operating system. Raritan's unique keyboard and mouse emulation ensures flawless operation.

Cascade CompuSwitch units to control up to 64 computers.

**CS2** – 2 Port

**CS4** – 4 Port

**CS8** – 8 Port

**CS4R** – 4 Port

Rack mount with cable support bracket

**CS8R** – 8 Port

Rack mount with cable support bracket

### The perfect switch for desktop or rack mount installations

The Raritan family of KVM (keyboard, video, mouse) switch products provides reliable, central control of multiple computers for the simplest to the most complex requirements. CompuSwitch is Raritan's economical, multi-platform, single-user KVM switch and is available with models for 2, 4, and 8 computers, expandable to control up to 64 computers. Its industrial strength, desktop and rack mount chassis makes CompuSwitch an ideal choice for corporate server rooms, computer test labs, and rack mount applications. CompuSwitch helps eliminate the cost and clutter of unnecessary equipment, reclaim space, improve operational productivity for a host of applications:

- ▶ Network server management
- ▶ Multi-workstation operation
- ▶ Hardware/software development and testing labs
- ▶ CTI and other OEM rack mount applications

### Premium performance and reliability

CompuSwitch is built with Raritan's unique, intelligent emulation technology, which dedicates an individual processor to each connected computer so that each computer always sees its own keyboard and mouse. This prevents keyboard and mouse lockups and ensures flawless boot up and operation of any mix of computers running any operating system.

CompuSwitch is available in 2-port, 4-port, and 8-port models. Connect any mix of PCs (PS/2 or AT), Sun, and Mac, running any operating system and cascade CompuSwitch units to control up to 64 computers. Raritan's unique keyboard and mouse emulation ensures flawless operation.

Installation is as easy as connecting computers with our tangle-proof, coaxial, ultra thin, double-shielded KVM cables, available in lengths of 0.6, 2, 4, 6, and 9m. Simply plug in your keyboard, monitor, and mouse to operate.

Selection of computers is done directly by touching the individual port buttons on the front panel of CompuSwitch, or by using hot-key commands from the keyboard. Standard features like AutoScan and AutoSkip make operation simple and convenient.



CS8R (Rack-mount chassis)

CompuSwitch 4 and 8-port models are also available in a 1U, industrial-strength, rack-mount chassis with a built-in cable support bracket for a neat, professional installation.

### Features

- ▶ High reliability, low cost, easy to use
- ▶ 2-port, 4-port, 8-port desktop models
- ▶ 4-port, 8-port models in 19" rack mount chassis (1U)
- ▶ Optional 19" rack mounting brackets for desktop models (1U)
- ▶ Optional rack mount extensions for 24" racks
- ▶ Dedicated keyboard and mouse emulator for each PC to ensure flawless boot up and operation
- ▶ Multi-platform-mix PC, Mac, Sun, Alpha®, RS/6000®, HP®9000, SGI®, ASCII devices; also USB support
- ▶ Support of any mix of computers – Windows® NT, Windows 2000, Novell® 4.x, UNIX®, Linux, or OpenVMS®
- ▶ Easy to manage, tangle-proof, high-resolution PC cables
- ▶ Supports VGA, SVGA, XGA high resolution video – 1600x1200
- ▶ Hot-key commands or individual channel buttons on front panel for convenient operation
- ▶ IntelliMouse® support
- ▶ SCAN for effortless monitoring
- ▶ SKIP to filter unused channels

### Specifications

<b>CS2 (2-port) CS4 (4-port)</b>	
<b>Dimensions</b>	268mm (W) x 200mm (D) x 44mm (H)
<b>Weight</b>	1,62 kg
<b>Power</b>	No external power required

<b>CS8 (8-port)</b>	
<b>Dimensions</b>	390mm (W) x 200mm (D) x 44mm (H)
<b>Weight</b>	2,24 kg
<b>Power</b>	No external power required

<b>CS4R (4-port rack mount with cable support bracket) CS8R (8-port rack mount with cable support bracket)</b>	
<b>Dimensions</b>	485mm (W) x 333mm (D) x 44mm (H)
<b>Weight</b>	2,8 kg
<b>Power</b>	No external power required

Optional DC Adapter - 6V/1.4A

**Warranty: Two Years** In addition Raritan offers two years extended warranty.

## Ready to manage smarter? Do it with Raritan's CompuSwitch.

Call +31 (0)10 284 4040 or visit [Raritan.eu/CompuSwitch](http://Raritan.eu/CompuSwitch)

Raritan is a leading provider of secure IT infrastructure management solutions. We offer IT and facility directors, managers and administrators the control they need to increase power management efficiency, improve data center productivity and enhance branch office operations. In over 50,000 locations worldwide, our integrated secure in-band and out-of-band products help companies monitor and manage their energy, servers and other IT devices. Our intelligent PDUs combined with energy management software and environmental sensors, offer remote power control and monitoring at the rack and device level, empowering data center owners with information to improve uptime and capacity planning, while efficiently utilizing energy to save power and money. And our access solutions, including KVM, serial and centralized management devices, offer unprecedented control of servers to maintain mission-critical environments. Raritan's OEM division provides embedded hardware and firmware for server and client management, including intelligent power management, KVM over IP, IPMI and other industry standards-based management applications.

Raritan has 38 offices worldwide, serving 76 countries. For more information, please visit [Raritan.eu](http://Raritan.eu)

©2009 Raritan Inc. All rights reserved. Raritan®, Know More. Manage Smarter.™ and CompuSwitch® are registered trademarks or trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners.

Specifications are subject to change without notice.