



TFBM7-3

ION™-B Series Extension Unit for Cellular 700

General Specifications

Brand	ION™-B
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type	Medium

Electrical Specifications

License Band	Cellular 700
Voltage Range	-60 to -36 Vdc

Electrical Specifications Rx (Uplink)

Operating Frequency Band 698 – 716 MHz (Cellular 700) | 776 – 787 MHz (Cellular 700)

Electrical Specifications Tx (Downlink)

Operating Frequency Band 728 – 757 MHz (Cellular 700)

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

TPSN3/28-80 — Power Supply Adapter ION™-B Series Remote Units, 80 W