



L4CLICK

Double Click-on Hanger for 1/2 in coaxial cable

Dimensions

Nominal Size	1/2 in
Compatible Diameter, maximum	16.256 mm 0.640 in
Compatible Diameter, minimum	15.240 mm 0.600 in
Height	51.00 mm 2.01 in
Length	89.00 mm 3.50 in
Width	45.00 mm 1.77 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Click-on hanger
Cables Per Hanger	2
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Package Quantity	10

Mechanical Specifications

Axial Load Capability, minimum with no cable slippage	≥5 times cable weight
Mounting	Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency

Packed Dimensions

Height	19.0 cm 7.5 in
Length	17.0 cm 6.7 in
Shipping Weight	0.26 kg 0.57 lb
Width	8.0 cm 3.1 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system