



L4SClick

Single Click-on Hanger for 1/2 in coaxial cable

Dimensions

Nominal Size	1/2 in
Compatible Diameter, maximum	16.256 mm 0.640 in
Compatible Diameter, minimum	15.240 mm 0.600 in
Height	25.00 mm 0.98 in
Length	51.00 mm 2.01 in
Width	48.00 mm 1.89 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Click-on hanger
Cables Per Hanger	2
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Package Quantity	10

Mechanical Specifications

Axial Load Capability, minimum with no cable slippage	≥5 times cable weight
Mounting	3/8 in (M10) drilled cable ladder
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency

Packed Dimensions

Height	17.6 cm 6.9 in
Length	8.2 cm 3.2 in
Shipping Weight	0.70 kg 1.54 lb
Width	10.8 cm 4.3 in

Regulatory Compliance/Certifications

Product Specifications

COMMScope®

L4SClick



Agency

ISO 9001:2008

Classification

Designed, manufactured and/or distributed under this quality management system