



L5SClickB

Single Click-on Hanger for 7/8 in coaxial cable, triple stack

Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	28.194 mm 1.110 in
Compatible Diameter, minimum	26.670 mm 1.050 in
Height	37.00 mm 1.46 in
Length	54.00 mm 2.13 in
Width	48.00 mm 1.89 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Click-on hanger
Cables Per Hanger	1
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Package Quantity	10

Mechanical Specifications

Axial Load Capability, minimum with no cable slippage	≥5 times cable weight
Mounting	3/8 in (M10) drilled cable ladder
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency

Packed Dimensions

Height	19.4 cm 7.6 in
Length	8.9 cm 3.5 in
Shipping Weight	0.50 kg 1.09 lb
Width	11.1 cm 4.4 in

Regulatory Compliance/Certifications

Product Specifications

COMMScope®

L5SCLICKB



Agency

ISO 9001:2008

Classification

Designed, manufactured and/or distributed under this quality management system