



## L7CLICK

Double Click-on Hanger for 1-5/8 in coaxial cable

### Dimensions

Nominal Size	1-5/8 in
Compatible Diameter, maximum	50.800 mm   2.000 in
Compatible Diameter, minimum	49.022 mm   1.930 in
Height	51.00 mm   2.01 in
Length	154.80 mm   6.09 in
Width	79.40 mm   3.13 in

### Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

### General Specifications

Hanger Type	Click-on hanger
Cables Per Hanger	1
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Package Quantity	10

### Mechanical Specifications

Axial Load Capability, minimum with no cable slippage	≥5 times cable weight
Mounting	3/8 in (M10) drilled cable ladder
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency

### Packed Dimensions

Height	12.9 cm   5.1 in
Length	5.9 cm   2.3 in
Shipping Weight	1.60 kg   3.53 lb
Width	5.5 cm   2.2 in

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system