



## 107655177 | M14MMO-246

**MMO Type Flush Mounted Angled Faceplate, four port ivory**

### Dimensions

|        |                     |
|--------|---------------------|
| Depth  | 32.77 mm   1.29 in  |
| Height | 144.53 mm   5.69 in |
| Weight | 0.16 kg   0.35 lb   |
| Width  | 83.31 mm   3.28 in  |

### Environmental Specifications

|                 |          |
|-----------------|----------|
| Safety Standard | cUL   UL |
|-----------------|----------|

### General Specifications

|                       |   |
|-----------------------|---|
| Color                 | Ivory   |
| Mount Type            | Flush   |
| Total Ports, quantity | 4   |
| Product Type          | Flush mount outlet  |
| Application           | has 45 degree angular ports for fiber and copper connectors |
| Package, quantity     | 1   |

### Mechanical Specifications

|               |  |
|---------------|--|
| Material Type | High-impact, flame retardant, UL-rated 94 V-0, thermoplastic |
|---------------|--|

### Regulatory Compliance/Certifications

|               |  |
|---------------|--|
| <b>Agency</b> | <b>Classification</b>  |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |