



107952442 | M104SMB-A-246

M104 Type Surface Mount Box, four port ivory

Dimensions

Depth	30.48 mm 1.20 in
Height	99.57 mm 3.92 in
Weight	0.10 kg 0.21 lb
Width	71.88 mm 2.83 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Mount Type	Surface
Product Type	Surface mount box
Application	Used with one to four M-Series modular information outlet
Color	Ivory
Package, quantity	1
Total Ports, quantity	4

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system