



108028457 | BP2100 BLANK PLATE PATCHMAX

PATCHMAX® BP2100 Blank Plate

Electrical Specifications

ANSI/TIA Category 5e

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Safety Standard cUL | UL

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand PATCHMAX® | SYSTIMAX®

Product Type Panel

Color Black

Package, quantity 1

Mechanical Specifications

Material Type Powder-coated steel

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC

ISO 9001:2008

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

