



108168469 | M12L-262

L Type Flush Mounted Faceplate, two port white

- Available for use with the DYMO® labeling solution

Dimensions

Depth	7.37 mm 0.29 in
Height	71.37 mm 2.81 in
Weight	0.04 kg 0.08 lb
Width	122.17 mm 4.81 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Color	White
Mount Type	Flush
Total Ports, quantity	2
Product Type	Flush mount modular faceplate
Application	Used with M-Series modular information outlet
Package, quantity	1

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system