



## 108685017 | M28L-246

**L Type Flush Mounted Double Gang Faceplate, eight port ivory**

- Available for use with the DYMO® labeling solution

### Dimensions

Depth	7.37 mm   0.29 in
Height	117.09 mm   4.61 in
Weight	0.06 kg   0.12 lb
Width	122.17 mm   4.81 in

### Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

### General Specifications

Color	Ivory
Mount Type	Flush
Total Ports, quantity	8
Product Type	Flush mount modular faceplate
Application	Used with M-Series modular information outlet
Package, quantity	1

### Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system