



760094003 | SC-47U-800-1000-SVF-DVR-NS-EMEA

Server Cabinet 47U 800 mm x 1000 mm (31.5 in x 39.4 in), Vented Steel Front Door, Double Vented Rear Door, Additional Bay

Dimensions

Depth	1000.0 mm 39.4 in
Height	2229.0 mm 87.8 in
Width	800.0 mm 31.5 in
Dimensional Standards	DIN 41491, part 1 (mounting dimensions) DIN 41494, part 7 EIA -310-E EN 60950 IEC 297-2 VDE 0100

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Ordering Note	Available in Europe, the Middle East, and Africa
Rack Units	47
Color	Black
Finish	Powder-coated, textured
Includes	All necessary attachment points, fitted Eight baying kits Forty screws, cage nuts and washers Four grounding squids, fitted M6 primary grounding point, fitted
Package, quantity	1
Packaging Type	Assembled

Mechanical Specifications

Door Material, front	Steel
Door Material, rear	Steel
Door Type, front	Single
Door Type, rear	Double
Baying Kit	Included
Cable Entry, top	One rectangular opening of 26082 mm ² Three openings total Two triangular openings of 7030 mm ² each
Door Vent, front	Vented/Fully perforated
Door Vent, rear	Vented/Split perforated
Frame Type	X-Frame
Grounding Kit	Included
Material Type	Steel
Side Panel Vent	Solid
Side Panels	Not included
Static Load Rating	1000.0 kg 2204.6 lb
Top Panel	Included
Top Panel Vent	Vented/Perforated

760094003 | SC-47U-800-1000-SVF-DVR-NS-EMEA

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

760079400 | BAYKIT — Baying Kit

760080366 | EARTHING-SQUID-KIT-4PK-EMEA — Earthing Squid Kit, 4 pack