



760143032 | SC 42U 800x1000 NS

**Server Bay Cabinet 42U 800 mm (32 inches) Wide x 1000 mm (40 inches) Deep, Steel
Fully Perforated Front, Split Perforated Rear**

Dimensions

Depth	1004.4 mm 39.5 in
Height	2000.5 mm 78.8 in
Width	797.0 mm 31.4 in
Dimensional Standards	EIA-310-E
Weight	1451.50 kg 3200.01 lb

General Specifications

Ordering Note	Available in Mexico, Central America, and South America Available in the United States and Canada
Rack Units	42
Color	Black
Finish	Powder-coated, textured
Includes	Fifty M6 clip nuts Four M12 leveling feet One hundred M6 screws
Package, quantity	1
Packaging Type	Assembled

Mechanical Specifications

Door Material, front	Steel
Door Material, rear	Steel
Door Type, front	Single
Door Type, rear	Double
Cable Entry, top	Four openings of 4 in (100 mm), with protective covers
Door Vent, front	Vented/Fully perforated
Door Vent, rear	Vented/Split perforated
Frame Type	Welded
Lock Type, front	2-Point
Lock Type, rear	1-Point
Material Type	Steel
Side Panels	Not included
Static Load Rating	1451.5 kg 3200.0 lb
Top Panel	Included
Top Panel Vent	Vented/Perforated

Packed Dimensions

Shipping Weight	111.10 kg 244.93 lb
-----------------	-----------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant

Product Specifications

COMMScope®

760143032 | SC 42U 800x1000 NS

ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system

