



760087551 | RFE-MOD-024-6F-MPO-LC02-KBL

ReadyPATCH® LC OptiSPEED® 24 Fiber Keyed Module, blue

- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

Construction Materials

Fiber Type	OptiSPEED®, 62.5 µm multimode fiber
Total Fibers, quantity	24

Dimensions

Depth	127.0 mm 5.0 in
Height	27.94 mm 1.10 in
Width	129.5 mm 5.1 in

Environmental Specifications

Safety Standard	UL
-----------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Keyed
Color, front	Blue
Adapters, quantity, front	12
Brand	ReadyPATCH®
Interface, rear	MPO
Adapters, quantity, rear	2
Interface Feature, rear	Standard
Color, rear	Gray
Package, quantity	1

Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	0.90 dB
Return Loss, minimum	20.0 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from 0 °C to +60 °C (+32 °F to +140 °F)